REFRIGERATION APPLICATION CHART (R12 AND R22)

Category: Technologie, Tester ok written by Lilianne | 17 May 2020 REFRIGERATION APPLICATION CHART (R12 AND R22)

| | | | NORMAL EVAPORTING TEMPERATURE DEGREES F | | | | | | | |
|-------|------|------|---|---------------|-----------|---------------|------------|---------------|------------|-------|
| H.P. | REF. | NOTE | -10 to +5 | | +5 to +20 | | +20 to +35 | | +35 to +50 | |
| 1/20 | R12 | S-F | 16 Ft. | TC-26 | 10 Ft. | TC-26 | | | Ĩ | |
| 1/12 | R12 | S-F | 12 Ft. | TC-26 | 12 Ft. | TC-31 | | | | |
| 1/9 | R12 | S | 12 Ft. | TC-26 | 12 Ft. | TC-31 | | | | |
| 1/9 | R12 | S | 10 Ft. | TC-26 | 10 Ft. | TC-31 | | | | |
| 1/8 | R12 | S-F | 10 Ft. | TC-26 | 10 Ft. | TC-31 | | | | |
| 1/6 | R12 | S | 12 Ft. | TC-31 | 12 Ft. | TC-36 | 8 Ft. | TC-36 | 10 Ft. | TC-42 |
| 1/6 | R12 | F | 10 Ft. | TC-31 | 10 Ft. | TC-36 | | | | |
| 1/5 | R12 | S | 10 Ft. | TC-31 | 10 Ft. | TC-36 | 7-1/2 Ft. | TC-42 | 7-1/2 Ft. | TC-49 |
| 1/5 | R12 | F | 8 Ft. | TC-31 | 8 Ft. | TC-36 | 10 Ft. | TC-42 | 6 Ft. | TC-42 |
| 1/4 | R22 | S-F | 12 Ft. | TC-36 | 6 Ft. | TC-36 | 8-1/2 Ft. | TC-42 | 6 Ft. | TC-49 |
| 1/4 | R12 | F | 10 Ft. | TC-36 | 6 Ft. | TC-36 | 8 Ft. | TC-42 | 6 Ft. | TC-49 |
| 1/3 | R22 | F | 10 Ft. | TC-36 | 6 Ft. | TC-36 | 11 Ft. | TC-49 | | |
| 1/3 | R12 | F | 12 Ft. | TC-42 | 6 Ft. | TC-42 | 9 Ft. | TC-49 | 6 Ft. | TC-54 |
| 1/2 | R22 | F | 6 Ft | TC-36 | 9 Ft. | TC-42 | 7-1/2 Ft. | TC-54 | 10 Ft. | TC-64 |
| 1/2 | R12 | F | 11 Ft. | TC-54 | 9 Ft. | TC-49 | | | | |
| 3/4 | R22 | F | 11 Ft. | TC-54 | 9 Ft. | TC-54 | | | | |
| 3/4 | R12 | F | 7-1/2 Ft. | TC-54 | 12 Ft. | TC-70 | 1 Ft. | TC-80 | | |
| 1 | R22 | F | 10 Ft. | TC-64 | 12 Ft. | TC-70 | | | | |
| 1 | R12 | F | 10 Ft. | TC-70 | 11 Ft. | TC-54 | 7-1/2 Ft. | TC-54 (2 pcs) | | |
| 1-1/2 | R22 | F | 7-1/2 Ft. | TC-54 (2 pcs) | 7-1/2 Ft. | TC-54 (2 pcs) | 8 Ft. | TC-64 (2 pcs) | | |
| 1-1/2 | R12 | F | | | 9 Ft. | TC-64 (2 pcs) | 10 Ft. | TC-80 (2 pcs) | | |
| 2 | R22 | F | | | 10 Ft. | TC-70 (2 pcs) | 9 Ft. | TC-75 (2 pcs) | | |
| 2 | R12 | F | 10 Ft. | TC-70 (2 pcs) | 9 Ft. | TC-75 (2 pcs) | 10 Ft. | TC-85 (2 pcs) | | |
| 3 | R22 | F | | | 10 Ft. | TC-70 (3 pcs) | 9 Ft. | TC-75 (3 pcs) | | |
| 3 | R12 | F | 10 Ft. | TC-70 (2 pcs) | 8 Ft. | TC-64 (4 pcs) | 10 Ft. | TC-80 (4 pcs) | | |
| 4 | R22 | F | | | 10 Ft. | TC-70 (4 pcs) | 9 Ft. | TC-75 (4 pcs) | | |
| 4 | R12 | F | | | 10 Ft. | TC-70 (5 pcs) | 9 Ft. | TC-75 (5 pcs) | | |
| 5 | R12 | F | | | 10 Ft. | TC-80 (5 pcs) | 9 Ft. | TC-85 (5 pcs) | | |

REFRIGERATION APPLICATION CHART (R-12 AND R-22)*

Private Picture Copyright : WWW.MBSM.PRO